

Clevis-Eye, Wide, Rotated 90-deg

By ANDERSON
Catalog # [CEW1353013](#)

Wide clevis eyes are used to attach suspension clamps to associated hardware in a single conductor VEE string assembly. Material: body - galvanized ductile iron, hardware - galvanized steel.

Features

"BNK" suffix if added replaces clevis pin & cotter pin with bolt, nut & cotter pin

General

Catalog Number	CEW1353013
Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Number of Bolt Holes	0
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate Body	0 lb

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Eye Hole	0.813 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in



*Representative Image

Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	2.875 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	2.6 lb
Width - Eye	1.438 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Specifications - CEW1353013](#)