

## Stud Connector, Bronze

By ANDERSON  
Catalog # [D2S1610012](#)

"Bolted Stud Connectors, Connecting Stud to Cable or Tube, Stud Dia./Thd.-1-1/2"-12, Copper Conductor Range: Cable-4/0 Sol.-2000 MCM, Cable Dia.- 0.460"- 1.632", Tubing IPS- 3/8" - 1-1/4", Material: Castings-Bronze Alloy, Hardware-Silicon Bronze or Stainless Steel"



### Features

- 0

### General

EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless & Galvanized Steel
Number of Stud Threads	12
Type	Studs
UPC	096359299677

### Dimensions

Diameter - Stud	1.75 in
Weight	8.987 lb

### Conductor Related

Conductor Diameter - Maximum	1.152 in
Conductor Diameter - Minimum	0.258 in
Conductor Diameter Range	0.258 - 1.152
Conductor Type	Copper

### Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - CC-1817 \(D2S Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)