

Stud Connector, Aluminum

By ANDERSON
Catalog # [DSATL2020G12](#)

"Bolted Expansion Stud Connectors, Connecting Aluminum Tubing to Copper Stud, Stud Dia./Thd.-3-1/4"-12, Tubing IPS-2-1/2", Material: Castings-Aluminum Alloy-Tube Clamping and Guide, Ball Bronze Alloy-Stud Clamping, Preformed Laminated Shunts-Copper (Tinned Contacts), Hardware-Stainless Steel and Galvanized Steel"



*Representative Image

Features

- "To specify 90 degree connector, add "90" to catalog number. Example: DSATL2020G9012
- To specify extra heavy (schedule 80 EHIPS) tubing, add "H" to catalog number. Example: DSATLH2020G12"

General

EU RoHS Indicator	No
Material	Aluminum
Material - Clamping Hardware	Stainless Steel
Number of Stud Threads	12
Type	Stud to Tube, Expansion
UPC	096359350064

Dimensions

Angle - Stud to Conductor	180 °
Diameter - Stud	2 in
Weight	21.364 lb

Conductor Related

Conductor Type	Aluminum Bus
----------------	--------------

Product Assets

- [Catalogs - Substation Connectors \(SA\)](#)
- [Sales Drawings - CC-4413 \(DSATL Product Family\)](#)
- [Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)
- [Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)