

Stud Connector, Aluminum

By ANDERSON
Catalog # [DSATLH4030G12](#)

"Bolted Stud Connectors, Connecting Stud to Two Cables or Tubes, Stud Dia./Thd.- 2"-12, Copper Conductor Range: Cable - 4/0 Sol.-2000 MCM, Cable Dia.- 0.460"- 1.632", Tubing IPS - 3/8" - 1-1/4", Material: Castings-Bronze Alloy, Hardware-Silicon Bronze or Stainless Steel"



*Representative Image

Features

- "To specify 90 degree connector, add "90" to catalog number. Example: DSATLH4030G9012"

General

Material	Aluminum
Material - Clamping Hardware	Stainless Steel
Number of Stud Threads	12
Type	Stud to Tube, Expansion

Dimensions

Angle - Stud to Conductor	180 °
Diameter - Stud	4 in
Weight	38.900 lb

Conductor Related

Conductor Type	Aluminum Bus
----------------	--------------

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)