

Stud Connector, Bronze

By ANDERSON
Catalog # [DSC11025123](#)

"Bolted Stud Connectors, Connecting Stud to Cable, Stud Dia./Thd.-1-1/2"-12, Copper Conductor Range- Cable- 250-1500-MCM, Dia-0.574"-1.412", Material: Castings-Bronze Alloy, Hardware-Silicon Bronze or Stainless Steel"



*Representative Image

Features

- "To specify 90 degree connector, insert "90" into catalog number. Example: DSC1102590123
- All sizes furnished with reversible cable caps"

General

EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Stud Threads	12
Type	Stud to Cable
UPC	096359346357

Dimensions

Angle - Stud to Conductor	180 °
Diameter - Clamping Hardware	0.375 in
Diameter - Stud	1.125 in
Weight	2.254 lb

Conductor Related

Conductor Diameter - Maximum	0.575 in
Conductor Diameter - Minimum	0.204 in
Conductor Diameter Range	0.204 - 0.575
Conductor Type	Copper

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - C-2888 \(DSC Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)