

HUBBELL

Power Systems

Stud Connector, Bronze

By ANDERSON

Catalog # [DSTF1206G12](#)

"Braided Shunt Bolted Expansion Stud Connectors, Connecting Stud To Tube, Stud Dia./Thd.-2"-12,Tubing IPS-3", Material: Castings-Bronze Alloy, Factory formed Laminated Shunts-Copper (Tinned Contacts),Hardware-Stainless Steel or Silicon Bronze"



Features

"To specify 90 degree connector, add "90" to catalog number
Example: DSTF1206G9012"

General

Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Ground Braid Lug Holes	0
Number of Stud Threads	12
Shunt Type	Braided Copper
Type	Studs

Dimensions

Angle - Stud to Conductor	180 °
Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Diameter - Stud	1.25 in
Length - Coupling	0 in
Length Before Compression	0 in

Electrical Ratings

Maximum Current Rating Amps 0
Continuous

Conductor Related

Conductor Type Copper Bus

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products](#)

[Video - Hubbell Power Systems Quick Ship](#)



A Hubbell brand