

Stud Connector, Bronze

By ANDERSON
Catalog # [DSTL202490G12](#)

"Tin Plated Bolted Stud Connectors, Connecting Stud to Cable or Tube, Stud Dia./Thd.-1-1/4"-0, Copper Conductor Range: Cable- #2-1000 MCM, Cable Dia.- 0.162"-.813", Tubing IPS- 3/8" - 3/4", Material: Castings-Bronze Alloy, Hardware-Silicon Bronze or Stainless Steel"



*Representative Image

Features

- "To specify braided shunt, replace "L" in catalog number with the letter "F" Example: DSTF2024G9012"

General

Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Stud Threads	12
Shunt Type	Laminated Copper
Type	Stud to Tube, Expansion

Dimensions

Angle - Stud to Conductor	90 °
Diameter - Stud	2 in
Weight	26.700 lb

Conductor Related

Conductor Type	Copper Bus
----------------	------------

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)