

Compression Splice Full Tension

By ANDERSON
Catalog # [FTR397](#)

Full Tension Aluminum splice for 397.5 (18/1) ACSR, 350 & 397.5 AAC



*Representative Image

Features

- Has positive center stop and tapered ends.

General

Compression Method	Conventional Die Tooling
Die Size	Burndy 327 or EEI-14A
EU RoHS Indicator	Contact Manufacturer
Inhibitor Loaded	Yes
Material	Aluminum Alloy
UPC	096359303886

Dimensions

Length Before Compression	22 in
Weight	1.470 lb

Conductor Related

Conductor Compatibility	ACSR-Merlin-336.4-18/1; ACSR-Linnet-336.4-26/7; ACSR-Oriole-336.4-30/7; ACSR-Chickadee-397.5-18/1; ACSR-Brahma-203.2-16/19; AAC-Canna-397.5-19
Conductor Diameter - Maximum	0.743
Conductor Diameter - Minimum	0.681
Conductor Diameter Range	0.681 - 0.743

Certifications and Compliance

UL Listed	No
-----------	----

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)