

GB2007B, Grounding Braid, 200A, Use with GC-109 Clamp

By ANDERSON
Catalog # [GB2007B](#)

Grounding Braid, 200A Flexible Cu Braid, Use with GC-109
Clamp.



Features

- Flexible copper grounding braid for use with GC109 ground clamp
- Braid is tinned with copper ferrule on each end
- One ferrule is drilled per NEMA standars and the other ferrule is blank

General

Connector Type	Braid
EU RoHS Indicator	No
Material	Copper
Material - Ferrules	Copper
Number of Ground Braid Lug Holes	2
UPC	096359305330
UPC 12 Digit	9635930533066

Dimensions

Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24 in
Weight	1.764 lb

Electrical Ratings

Amperage Rating	200
Rating - Indoor Amperage	340 A
Rating - Outdoor Amperage	405 A

Certifications and Compliance

Certification - CSA Approved	N
Certification - ETL	N
Certification - UL Recognized	N
Certification - cULus	N
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Pallet Quantity	960
-----------------	-----

Product Assets

[Sales Drawings - 50029523](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)