

Grounding Clamp

By ANDERSON
Catalog # [GC11021D](#)

Bronze alloy ground clamp for clamping one, two or three cables to rod or tube



*Representative Image

Features

"Everdur hardware supplied by adding Suffix "ED"
e.g.GC11021DED"

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	GC11021D
EU RoHS Indicator	No
Material	Bronze
Material - Hardware	Stainless Steel
UPC	096359350927

Dimensions

Diameter - Clamping Hardware	0.5 in
Diameter - Rod / Tube	0.5 in
Diameter - Rod / Tube Outside	0.75 in

Weight	0.686 lb
--------	----------

Conductor Related

Conductor Diameter - Maximum	0.419 in
Conductor Diameter - Minimum	0.204 in
Conductor Diameter Range	0.204 - 0.419
Conductor Type	Copper

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

Product Assets

- [Sales Drawings - C-2336 \(GC-110 and AGC-110 Product Family\)](#)
- [Specifications - GC11021D](#)
- [Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products](#)
- [Video - Hubbell Power Systems Quick Ship](#)