

Support Bracket

By ANDERSON
Catalog # [GWB1S](#)

Bracket, Ductile Iron, Galvanized, UTS 5,000 pounds vertical loading, for supporting ground wire suspension clamp. Bracket supplied with one LK30 Forged Chain Link (1.000 x 2.125" Opening x 0.500" Thick)



*Representative Image

Features

- Designed to be used with most types of suspension clamps (aluminum or ferrous)
- May be mounted with 3/4" dia through bolt and 1/2" dia lag screw

General

Material - Clamp	Ductile Iron
Material - Hardware	Galvanized Steel
Product Category	Bracket
Strength Rating - Ultimate Body	5000 lb
UPC	096359314059

Dimensions

Diameter - Clamping Hardware	0 in
Diameter - Lag Screw - Maximum	0.5 in
Diameter - Mounting Bolt - Maximum	0.75 in
Dimensions	5.5 in x 4 in x 4 in
Height	4 in
Length	5.5 in
Mounting Bolt Spacing	3.31 in
Nominal Guy Wire Size	0 in
Weight	2.45 lb
Width	4 in

Logistics

Pallet Quantity	405
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)
[Sales Drawings - CC5027](#)
[Technical Solutions - AN-GWB1S-SPEC-EN](#)