

Grounding Clamp

By ANDERSON
Catalog # [GC143G1](#)

Bronze alloy ground clamp for clamping a copper cable to flat bar. Cable groove in bottom piece prevents excessive cable distortion.



*Representative Image

Features

- Bolts furnished are for clamping
- Silicon Bronze hardware supplied by adding Suffix ED
- If longer bolts are required, add bar thickness to catalog number, Example: GC143G112 for 1/2” bar

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	GC143G1
EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Galvanized Steel
Material - Hardware	Galvanized Steel
UPC	096359307068

Dimensions

Weight0.588 lb

Conductor Related

Conductor Diameter - Maximum	0.419 in
Conductor Diameter - Minimum	0.204 in
Conductor Diameter Range	0.204 - 0.419
Conductor Type	Copper

Certifications And Compliance

Buy America(n) QualifiedContact Manufacturer

Product Assets

[Sales Drawings - C-2630 \(GC143 Product Family\)](#)
[Specifications - GC143G1](#)
[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products](#)
[Video - Hubbell Power Systems Quick Ship](#)