

Suspension Clamp

By ANDERSON
Catalog # [HAS118N](#)

"The HAS suspension clamp is a saddle type suspension clamp designed for use on standard voltage transmission lines. The HAS clamps are designed for use with all aluminum, ACSR, or aluminum alloy conductor. Material: Clamp-Aluminum alloy. Clamping Range: 1.400"-2.130""



*Representative Image

Features

- "Bolt and nut may be substituted for clevis pin by adding suffix "BNK" to catalog number
- The clevis bolt and clevis pin are the same diameter"

General

| | |
|--|------------------------------------|
| Bolt Installation Torque (Recommended) | 480 in-lbs |
| Fitting Type | None |
| Material - Clamp | Aluminum |
| Material - Hardware | Galvanized Steel |
| Material - Pin | Stainless Steel |
| Material - Pin (Cotter) | Stainless Steel |
| Product Category | Suspension Clamp |
| Strength Rating - Ultimate Body | 25000 lb |
| Type | Standard Voltage Suspension Clamps |
| U-Bolts | 1/2 in |
| UPC | 096359314790 |

Dimensions

| | |
|--------------------------|------------|
| Angle - Take-Off Maximum | 22.5 ° |
| Clamping - Maximum | 1.18 in |
| Clamping - Minimum | 0.7 in |
| Clevis Opening | 1.03125 in |
| Diameter - Clevis Pin | 0.625 in |
| Height | 2.75 in |
| Length | 8 in |
| Weight | 3.38 lb |

Electrical Ratings

| | |
|---------------------|----------|
| Voltage Application | Standard |
|---------------------|----------|

Conductor Related

| | |
|-------------------------|--|
| Clamping Range | 0.7- 1.18 |
| Conductor Compatibility | ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Parakeet-556.5-24/7;ACSR-Dove-556.5-26/7;ACSR-Eagle-556.5-30/7;ACSR-Peacock-605-24/7;ACSR-Squab-605-26/7;ACSR-Teal-605-30/19;ACSR-Kingbird-636-18/1;ACSR-Swift-636-36/1;ACSR-Rook-636-24/7;ACSR-Grosbeak-636-26/7;ACSR-Egret-636-30/19;ACSR-Flamingo-666.6-24/7;ACSR-Gannet-666.6-26/7;ACSR-Stilt-715.5-24/7;ACSR-Starling-715.5-26/7;ACSR-Redwing-715.5-30/19;ACSR-Coot-795-36/1;ACSR-Cuckoo-795-24/7;ACSR-Drake-795-26/7;ACSR-Tern-795-45/7;ACSR-Condor-795-54/7;ACSR-Mallard-795-30/19;ACSR-Ruddy-900-45/7;ACSR-Canary-900-54/7;ACSR-Rail-954-45/7;ACSR-Brahma-203.2-16/19;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Daffodil-350-19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-77;AAC-Zinnia- |

Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37;AAC-Orchid-636-37;AAC-Flag-700-61;AAC-Violet-715.5-37;AAC-Nasturtium-715.5-61;AAC-Cattail-750-61;AAC-Arbutus-795-37;AAC-Lilac-795-61;AAC-Cockscomb-900-37;AAC-Snapdragon-900-61;AAC-Magnolia-954-37;AAC-Goldenrod-954-61;AAC-Camellia-1000-61;AAC-Bluebell-1033.5-37;AAC-Larkspur-1033.5-61;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18;ACAR-653.1-12/7;ACAR-739.8-18/19;ACAR-853.7-30/7;ACAR-1024.5-30/7

Logistics

Pallet Quantity 576

Product Assets

Catalogs - Transmission Connectors Catalog - Full (CA05063E)
Literature - Ropes Course Industry Letter (April 2021)
Sales Drawings - HAS-118-N CUTSHEET
Sales Drawings - HAS Product Family
Technical Solutions - AN-HAS118N-SPEC-EN



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
AN-HAS118N-SPEC-EN | REV 1/2024