

## Automatic Guy Wire Deadend, 3/16" EHS

By ANDERSON  
Catalog # [GDE5199](#)



Automatic Guy Wire Deadend, 3/16", HSS, EHS, Common,  
Siemens-Martin, Utilities and Bell System Strand

\*Representative Image

### Features

- Fargo GDE5200 Series Automatic deadends are designed for use on all grades of galvanized steel wire strand ... High Strength, Extra High Strength, Alumoweld®, Aluminized, Common, Siemens-Martin, Utilities and Bell System Strand.
- Innovative yoke design allows for installation without use of a gripping hook
- Use suffix "L" for long bail

### General

Bail Option	Standard
Material	Aluminum Alloy; Steel
Material - Bail	Stainless Steel
Material - Jaw	HS Plated Steel
Material - Shell	High Strength Aluminum Alloy
Material - Yoke	Aluminum Alloy
Product Category	Guy Wire
Type	Automatic
UPC	096359529712

### Dimensions

Nominal Guy Wire Size	3/16" 7 Strand
-----------------------	----------------

### Conductor Related

Conductor Diameter - Maximum	0.188
Conductor Diameter - Minimum	0.174
Conductor Diameter Range	0.174 - 0.188

### Logistics

Carton Quantity	50
Pallet Quantity	2400

### Product Assets

[Catalogs - Communications Catalog \(CA12042E\)](#)  
[Catalogs - Distribution Connectors \(CA05127E\)](#)  
[Installation Manuals - GDE52xx Guy Wire Automatic Deadends - installation instructions](#)  
[Literature - Ropes Course Industry Letter \(April 2021\)](#)  
[Sales Drawings - GDE520x Sales Drawing](#)  
[Sales Drawings - GDE51xx Sales Drawing](#)  
[Technical Solutions - AN-GDE5199-SPEC-EN](#)

### Related Products

[FWDE1102 - Formed Wire Deadend for Guy Strand 3/16"](#)