

HUBBELL Power Systems

Suspension Clamp

By ANDERSON
Catalog # [HAC204N](#)

For standard voltage angle construction with all aluminum, ACSR, or alluminum alloy conductors. See catalog reference section for maximum conductor temperature guidelines. Recommended for torque on U-Bolts: 1/2" - 480 in-lb; 5/8" - 720 in-lb



Features

- "Bolt and nut may be substituted for clevis pin by adding suffix "BNK" to catalog number
- The clevis bolt and clevis pin are the same diameter"

General

Bolt Installation Torque (Recommended)	480 in-lbs
Catalog Number	HAC204N
EU RoHS Indicator	No
Fitting Type	None
Material - Clamp	Aluminum
Material - Hardware	Galvanized Steel
Material - Pin	Stainless Steel
Material - Pin (Cotter)	Stainless Steel
Product Category	Suspension Clamp
Strength Rating - Ultimate	40000 lb
Body Type	Standard Voltage Suspension Clamps
U-Bolts	1/2 in
UPC	096359314707

Dimensions

Angle - Take-Off Maximum	35 °
Clamping - Maximum	2.04 in
Clamping - Minimum	1.73 in
Clevis Opening	2.171875 in
Diameter - Clevis Pin	0.75 in
Height	3.5 in
Length	11.25 in
Weight	5.6 lb

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Clamping Range	1.73- 2.04
Conductor Compatibility	ACSR-Mallard-795-30/19;ACSR-Ruddy-900-45/7;ACSR-Canary-900-54/7;ACSR-Rail-954-45/7;ACSR-Cardinal-954-54/7;ACSR-Ortolan-1033.5-45/7;ACSR-Curlew-1033.5-54/7;ACSR-Bluejay-1113-45/7;ACSR-Finch-1113-54/19;ACSR-Bunting-1192.5-45/7;ACSR-Bluebird-2156-84/19;ACSR-Kiwi-2167-72/7;ACSR-Thrasher-2312-76/19;ACSR-Joree-2515-76/19;AAC-Magnolia-954-37;AAC-Goldenrod-954-61;AAC-Camellia-1000-61;AAC-Bluebell-1033.5-37;AAC-Larkspur-1033.5-61;AAC-Marigold-1113-61;AAC-Hawthorn-1192.5-61;AAC-Narcissus-1272-61;AAC-Lupine-2500-91;ACAR-1024.5-30/7;ACAR-1109-30/7;ACAR-1172-30/7;ACAR-1172-18/19;ACAR-2493-72/19;ACAR-2493-54/37

Logistics

Pallet Quantity	108
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Literature - Ropes Course Industry Letter \(April 2021\)](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-HAC204N-SPEC-EN | REV 6/2024