

Suspension Clamp

By ANDERSON
Catalog # [HAS213C](#)

"The HAST2 suspension clamp is a double groove, saddle type suspension clamp designed for use on standard voltage T2 transmission lines. Type HAST2 is recommended for AAC, ACSR, or AAAC T2 conductors. Maximum conductor temperature 130°C. Material: Clamp-Aluminum alloy, Clevis-Galvanized Ductile iron. Clamping Range: 0.522"-0.642"



*Representative Image

Features

- "Bolt and nut may be substituted for clevis pin by adding suffix "BNK" to catalog number
- The clevis bolt and clevis pin are the same diameter
- "C" suffix indicates the suspension clamp will contain the clevis eye CA16"

General

Bolt Installation Torque (Recommended)	720 in-lbs
EU RoHS Indicator	No
Fitting Type	Clevis
Material - Clamp	Aluminum
Material - Hardware	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Material - Socket and Clevis	Galvanized Ductile Iron
Product Category	Suspension Clamp
Strength Rating - Ultimate Body	25000 lb
Type	Standard Voltage Suspension Clamps
U-Bolts	5/8 in
UPC	096359386469

Dimensions

Angle - Take-Off Maximum	22 °
Clamping - Maximum	2.13 in
Clamping - Minimum	1.4 in
Clevis Opening	2.25 in
Diameter - Clevis Pin	0.625 in
Height	3.63 in
Length	10.50 in
Weight	8.0 lb

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Clamping Range	1.4- 2.13
----------------	-----------

Logistics

Pallet Quantity	150
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - HAS Product Family](#)
[Technical Solutions - AN-HAS213C-SPEC-EN](#)