

Suspension Clamp

By ANDERSON
Catalog # [HAS147C](#)



The HAS suspension clamp is a saddle type suspension clamp designed for use on standard voltage transmission lines. The HAS clamps are designed for use with all aluminum, ACSR, or aluminum alloy conductor. Material: Clamp-Aluminum alloy, Clevis-Galvanized Ductile iron. Clamping Range: 2.000-2.520

Features

- "Bolt and nut may be substituted for clevis pin by adding suffix "BNK" to catalog number
- The clevis bolt and clevis pin are the same diameter
- "C" suffix indicates the suspension clamp will contain the clevis eye CA13"

General

Bolt Installation Torque (Recommended)	480 in-lbs
Catalog Number	HAS147C
EU RoHS Indicator	No
Fitting Type	Clevis
Material - Clamp	Aluminum
Material - Hardware	Galvanized Steel
Material - Pin	Stainless Steel
Material - Pin (Cotter)	Stainless Steel
Material - Socket and Clevis	Galvanized Ductile Iron
Product Category	Suspension Clamp
Strength Rating - Ultimate	25000 lb
Body	
Type	Standard Voltage Suspension Clamps
U-Bolts	1/2 in
UPC	096359351290

Dimensions

Angle - Take-Off Maximum	22.5 °
Clamping - Maximum	1.47 in
Clamping - Minimum	1 in
Clevis Opening	1.5625 in
Diameter - Clevis Pin	0.625 in
Height	3.125 in
Length	9.1875 in
Weight	5.3 lb

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Clamping Range	1- 1.47
----------------	---------

Conductor Compatibility

ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Parakeet-556.5-24/7;ACSR-Dove-556.5-26/7;ACSR-Eagle-556.5-30/7;ACSR-Peacock-605-24/7;ACSR-Squab-605-26/7;ACSR-Kingbird-636-18/1;ACSR-Swift-636-36/1;ACSR-Egret-636-30/19;ACSR-Flamingo-666.6-24/7;ACSR-Gannet-666.6-26/7;ACSR-Stilt-715.5-24/7;ACSR-Starling-715.5-26/7;ACSR-Redwing-715.5-30/19;ACSR-Coot-795-36/1;ACSR-Cuckoo-795-24/7;ACSR-Drake-795-26/7;ACSR-Tern-795-45/7;ACSR-Condor-795-54/7;ACSR-Mallard-795-30/19;ACSR-Ruddy-900-45/7;ACSR-Canary-900-54/7;ACSR-Rail-954-45/7;ACSR-Cardinal-954-54/7;ACSR-Ortolan-1033.5-45/7;ACSR-Curlew-1033.5-54/7;ACSR-Bluejay-1113-45/7;ACSR-Finch-1113-54/19;ACSR-Bunting-1192.5-45/7;ACSR-Grackle-1192.5-

54/19;ACSR-Bittern-1272-
45/7;ACSR-Pheasant-1272-
54/19;ACSR-Dipper-1351.5-
45/7;ACSR-Martin-1351.5-
54/19;ACSR-Bobolink-1431-
45/7;ACSR-Plover-1431-
54/19;ACSR-Nuthatch-1510.5-
45/7;ACSR-Brahma-203.2-
16/19;AAC-Daffodil-350-
19;AAC-Canna-397.5-19;AAC-
Cosmos-477-19;AAC-Syringa-
477-37;AAC-Zinnia-500-
19;AAC-Hyacinth-500-37;AAC-
Dahlia-556.5-19;AAC-Mistletoe-
556.5-37;AAC-Meadowsweet-
600-37;AAC-Orchid-636-
37;AAC-Flag-700-61;AAC-
Arbutus-795-37;AAC-Lilac-795-
61;AAC-Cockscomb-900-
37;AAC-Snapdragon-900-
61;AAC-Magnolia-954-37;AAC-
Goldenrod-954-61;AAC-
Camellia-1000-61;AAC-
Bluebell-1033.5-37;AAC-
Larkspur-1033.5-61;AAC-

Marigold-1113-61;AAC-
Hawthorn-1192.5-61;AAC-
Narcissus-1272-61;AAC-
Columbine-1351.5-61;AAC-
Carnation-1431-61;AAC-
Gladiolus-1510.5-61;AAC-
Coreopsis-1590-61;ACAR-653.1-
12/7;ACAR-853.7-30/7;ACAR-
1024.5-30/7;ACAR-1109-
30/7;ACAR-1172-30/7;ACAR-
1172-18/19

Certifications And Compliance

Buy America(n) Qualified

Contact Manufacturer

Logistics

Carton Quantity

10

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)

[Literature - Ropes Course Industry Letter \(April 2021\)](#)

[Sales Drawings - HAS Product Family](#)

[Specifications - HAS147C](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
AN-HAS147C-SPEC-EN | REV 3/2025