

HUBBELL Power Systems

Hot Line, Clevis Ball

By ANDERSON
Catalog # [HBC30](#)

Hot line ball clevises are used to attach ball and socket insulators to other associated hardware within an insulator string. Shoulders are provided to accommodate hot line tools.



*Representative Image

Features

- "For use with ANSI class 52-3 & 52-5 insulators
- Material: Body-Galvanized Forged steel, Clevis Pin-Galvanized steel, Cotter pin-Stainless steel
- Bolt and nut may be substituted for clevis pin by adding suffix "BNK" to catalog number
- Shield nut can be supplied by adding suffix "SN" to catalog number"

General

Catalog Number	HBC30
Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	HBC Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359315377

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Dimensions	9.56 in x 1.63 in x 1.63 in
Height	1.63 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length	9.56 in
Length - Coupling	9.563 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	2.45 lb
Width	1.63 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Logistics

Pallet Quantity	864
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)
[Sales Drawings - HBC30 CUTSHEET](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-HBC30-SPEC-EN | REV 6/2024