

Suspension Clamp

By ANDERSON
Catalog # [HAS162N](#)

"The HAS suspension clamp is a saddle type suspension clamp designed for use on standard voltage transmission lines. The HAS clamps are designed for use with all aluminum, ACSR, or aluminum alloy conductor. Material: Clamp-Aluminum alloy. Clamping Range: 0.200"-0.620"



*Representative Image

Features

- "Bolt and nut may be substituted for clevis pin by adding suffix "BNK" to catalog number
- The clevis bolt and clevis pin are the same diameter"

General

Bolt Installation Torque (Recommended)	480 in-lbs
EU RoHS Indicator	No
Fitting Type	None
Material - Clamp	Aluminum
Material - Hardware	Galvanized Steel
Material - Pin	Stainless Steel
Material - Pin (Cotter)	Stainless Steel
Product Category	Suspension Clamp
Strength Rating - Ultimate Body	25000 lb
Type	Standard Voltage Suspension Clamps
U-Bolts	1/2 in
UPC	096359314943

Dimensions

Angle - Take-Off Maximum	22.5 °
Clamping - Maximum	1.62 in
Clamping - Minimum	1.1 in
Clevis Opening	1.1875 in
Diameter - Clevis Pin	0.625 in
Height	3.078125 in
Length	9.5 in
Weight	3.8 lb

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Clamping Range	1.1- 1.62
Conductor Compatibility	ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Parakeet-556.5-24/7;ACSR-Dove-556.5-26/7;ACSR-Eagle-556.5-30/7;ACSR-Peacock-605-24/7;ACSR-Squab-605-26/7;ACSR-Teal-605-30/19;ACSR-Kingbird-636-18/1;ACSR-Swift-636-36/1;ACSR-Rook-636-24/7;ACSR-Grosbeak-636-26/7;ACSR-Flamingo-666.6-24/7;ACSR-Drake-795-26/7;ACSR-Mallard-795-30/19;ACSR-Ruddy-900-45/7;ACSR-Canary-900-54/7;ACSR-Rail-954-45/7;ACSR-Cardinal-954-54/7;ACSR-Ortolan-1033.5-45/7;ACSR-Curlew-1033.5-54/7;ACSR-Bluejay-1113-45/7;ACSR-Finch-1113-54/19;ACSR-Bunting-1192.5-45/7;ACSR-Grackle-1192.5-54/19;ACSR-Bittern-1272-45/7;ACSR-Pheasant-1272-54/19;ACSR-Dipper-1351.5-45/7;ACSR-Martin-1351.5-54/19;ACSR-Bobolink-1431-45/7;ACSR-Plover-1431-54/19;ACSR-Nuthatch-1510.5-45/7;ACSR-Parrot-1510.5-54/19;ACSR-Lapwing-1590-45/7;ACSR-Falcon-1590-54/19;ACSR-Chukar-1780-84/19;ACSR-Brahma-203.2-16/19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-77;AAC-Dahlia-556.5-19;AAC-

37; AAC-Damian-556.5-19; AAC-Mistletoe-556.5-37; AAC-Meadowsweet-600-37; AAC-Orchid-636-37; AAC-Flag-700-61; AAC-Violet-715.5-37; AAC-Nasturtium-715.5-61; AAC-Cattail-750-61; AAC-Magnolia-954-37; AAC-Goldenrod-954-61; AAC-Camellia-1000-61; AAC-Bluebell-1033.5-37; AAC-Larkspur-1033.5-61; AAC-Marigold-1113-61; AAC-Hawthorn-1192.5-61; AAC-Narcissus-1272-61; AAC-Columbine-1351.5-61; AAC-Carnation-1431-61; AAC-Gladiolus-1510.5-61; AAC-Coreopsis-1590-61; ACAR-653.1-12/7; ACAR-739.8-18/19; ACAR-1024.5-30/7; ACAR-1109-30/7; ACAR-1172-30/7; ACAR-1172-18/19; ACAR-1933-42/19

Logistics

Pallet Quantity 120

Product Assets

Catalogs - Transmission Connectors Catalog - Full (CA05063E)
Literature - Ropes Course Industry Letter (April 2021)
Sales Drawings - HAS Product Family
Technical Solutions - AN-HAS162N-SPEC-EN



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
AN-HAS162N-SPEC-EN | REV 1/2024