

# HUBBELL Power Systems

## Suspension Clamp

By ANDERSON  
Catalog # [HAS213S](#)

The HAS suspension clamp is a saddle type suspension clamp designed for use on standard voltage transmission lines. The HAS clamps are designed for use with all aluminum, ACSR, or aluminum alloy conductor. Material: Clamp-Aluminum alloy, Socket-Galvanized Ductile iron. Clamping Range: 0.400-0.850



### Features

- "Bolt and nut may be substituted for clevis pin by adding suffix "BNK" to catalog number
- The clevis bolt and clevis pin are the same diameter
- "S" suffix indicates the suspension clamp will contain the socket eye SA16"

### General

Bolt Installation Torque (Recommended)	720 in-lbs
Catalog Number	HAS213S
EU RoHS Indicator	No
Fitting Type	Socket
Material - Clamp	Aluminum
Material - Hardware	Galvanized Steel
Material - Pin	Stainless Steel
Material - Pin (Cotter)	Stainless Steel
Material - Socket and Clevis	Galvanized Ductile Iron
Product Category	Suspension Clamp
Strength Rating - Ultimate	25000 lb
Body	
Type	Standard Voltage Suspension Clamps
U-Bolts	5/8 in
UPC	096359378778

### Dimensions

Angle - Take-Off Maximum	22 °
Clamping - Maximum	2.13 in
Clamping - Minimum	1.4 in
Clevis Opening	2.25 in
Diameter - Clevis Pin	0.625 in
Height	3.625 in
Length	10.5 in
Weight	9.134 lb

### Electrical Ratings

Voltage Application	Standard
---------------------	----------

## Conductor Related

Clamping Range 1.4- 2.13  
Conductor Compatibility ACSR-Parakeet-556.5-24/7;ACSR-Dove-556.5-26/7;ACSR-Eagle-556.5-30/7;ACSR-Peacock-605-24/7;ACSR-Squab-605-26/7;ACSR-Teal-605-30/19;ACSR-Kingbird-636-18/1;ACSR-Swift-636-36/1;ACSR-Rook-636-24/7;ACSR-Grosbeak-636-26/7;ACSR-Egret-636-30/19;ACSR-Flamingo-666.6-24/7;ACSR-Gannet-666.6-26/7;ACSR-Stilt-715.5-24/7;ACSR-Starling-715.5-26/7;ACSR-Redwing-715.5-30/19;ACSR-Coot-795-36/1;ACSR-Cuckoo-795-24/7;ACSR-Drake-795-26/7;ACSR-Tern-795-45/7;ACSR-Condor-795-54/7;ACSR-Mallard-795-30/19;ACSR-Ruddy-900-45/7;ACSR-Canary-900-54/7;ACSR-Rail-954-45/7;ACSR-Cardinal-954-54/7;ACSR-Ortolan-1033.5-45/7;ACSR-Curlew-1033.5-54/7;ACSR-Bluejay-1113-45/7;ACSR-Finch-1113-54/19;ACSR-Bunting-1192.5-45/7;ACSR-Grackle-1192.5-54/19;ACSR-Bittern-1272-45/7;ACSR-Pheasant-1272-54/19;ACSR-Dipper-1351.5-45/7;ACSR-Martin-1351.5-54/19;ACSR-Bobolink-1431-45/7;ACSR-Plover-1431-54/19;ACSR-Nuthatch-1510.5-45/7;ACSR-Parrot-1510.5-54/19;ACSR-Lapwing-1590-45/7;ACSR-Falcon-1590-54/19;ACSR-Chukar-1780-84/19;ACSR-Bluebird-2156-84/19;ACSR-Kiwi-2167-72/7;ACSR-Thrasher-2312-76/19;ACSR-Joree-2515-76/19;AAC-Orchid-636-37;AAC-Flag-700-61;AAC-Violet-715.5-37;AAC-Nasturtium-715.5-61;AAC-Cattail-750-61;AAC-Arbutus-795-37;AAC-Lilac-795-61;AAC-Cockscomb-900-37;AAC-Snapdragon-900-61;AAC-Magnolia-954-37;AAC-Goldenrod-954-61;AAC-Camellia-1000-61;AAC-Bluebell-1033.5-37;AAC-Larkspur-1033.5-61;AAC-Marigold-1113-61;AAC-Hawthorn-1192.5-61;AAC-Narcissus-1272-61;AAC-

## Logistics

Pallet Quantity 150

## Product Assets

[Catalogs - Transmission Connectors Catalog - Full Literature - Ropes Course Industry Letter \(April 2021\)](#)  
[Sales Drawings - HAS Product Family](#)

Columbine-1351.5-61;AAC-  
Carnation-1431-61;AAC-  
Gladiolus-1510.5-61;AAC-  
Coreopsis-1590-61;AAC-  
Cowslip-2000-91;AAC-Lupine-  
2500-91;ACAR-653.1-  
12/7;ACAR-739.8-18/19;ACAR-  
853.7-30/7;ACAR-1024.5-  
30/7;ACAR-1109-30/7;ACAR-  
1172-30/7;ACAR-1172-  
18/19;ACAR-1933-42/19;ACAR-  
2493-72/19;ACAR-2493-54/37



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-HAS213S-SPEC-EN | REV 6/2024