

## Suspension Clamp, Double Groove, Bolted Aluminum

By ANDERSON  
Catalog # [HAST2252N](#)



Made with double groove keeper to accommodate twin conductor. For standard voltage application with all aluminum, ACSR, or aluminum alloy conductor. Maximum conductor temperature 130 C.

### Features

- "Bolt and nut may be substituted for clevis pin by adding suffix "BNK" to catalog number
- The clevis bolt and clevis pin are the same diameter"

### General

Bolt Installation Torque (Recommended)	720 in-lbs
Catalog Number	HAST2252N
EU RoHS Indicator	No
Fitting Type	None
Material - Clamp	Aluminum
Material - Hardware	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Product Category	Suspension Clamp
Strength Rating - Ultimate	25000 lb
Body	
Type	Standard Voltage/T2 Suspension Clamps
UPC	096359406952

### Dimensions

Angle - Take-Off Maximum	17.5 °
Clamping - Maximum	1.165 in

Clamping - Minimum	0.977 in
Clevis Opening	2.68 in
Diameter - Clevis Pin	0.625 in
Height	4.25 in
Length	12 in
Weight	10 lb

### Electrical Ratings

Voltage Application	Standard
---------------------	----------

### Conductor Related

Clamping Range	0.977- 1.165
----------------	--------------

### Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
--------------------------	----------------------

### Logistics

Pallet Quantity	90
-----------------	----

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)  
[Literature - Ropes Course Industry Letter \(April 2021\)](#)  
[Specifications - HAST2252N](#)