

Hot Line Link, Y-Clevis Ball

By ANDERSON
Catalog # [HYBC30](#)

Hot line ball clevises are used to attach ball and socket insulators to other associated hardware within an insulator string. Shoulders are provided to accommodate hot line tools and the bent bolt in the Y-section provides an additional point of articulation within an assembly.

Features

- "Material: Body-Galvanized steel, Clevis Pin-Galvanized steel, Cotter Pin-Stainless steel
- For use with ANSI class 52-3 & 52-5 insulators
- Shield nut can be supplied by adding suffix "SN" to catalog number"

General

Catalog Number	HYBC30
Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	HYBC Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359317418

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Dimensions	2.272 in x 1.5 in x 1.314 in
Height	1.314 in



*Representative Image

Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length	2.272 in
Length - Coupling	9.313 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	2.891 lb
Width	1.5 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Logistics

Pallet Quantity	720
-----------------	-----

Product Assets

- [Catalogs - Transmission Connectors Catalog - Full](#)
- [Sales Drawings - HYBC-30 CUTSHEET](#)
- [Specifications - HYBC30](#)