

Hook, Suspension Ball

By ANDERSON  
Catalog # [HB30](#)

Suspension hooks are used to attach ball and socket or clevis insulators directly to the tower attachment pad. All hooks are of the self-locking design.



Features

- Self-locking design
- Ultimate Strength is 30,000 lbs. (133 Kn)
- 2 inch length
- Material: Galvanized Forged Steel
- For use with ANSI Class 52-3 and 52-5 clevis type insulators per ANSI Spec. C29.2-71.

General

Catalog Number	HB30
Material	Steel
Number of Bolt Holes	0
Series	HB Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359315292

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Dimensions	3.188 in x 3 in x 0.719 in

Height	0.719 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length	3.188 in
Length - Coupling	2 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	1.372 lb
Width	3 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)  
[Sales Drawings - HB30](#)  
[Specifications - HB30](#)