

HUBBELL Power Systems

Compression Terminal Straight, Partial Tension

By ANDERSON
Catalog # JTS10

Jumper terminals are prefilled with inhibitor. Tongue holes have NEMA spacing. Standard hardware includes one aluminum 1/2 - 13 bolt, nut, and two aluminum washers per .56 diameter hole. Jumper terminals for conductors 1.00 inch diameter or larger are EHV rated.

Features

- "Jumper terminals are prefilled with inhibitor
- Standard hardware includes Aluminum 1/2-13 bolt, nut and two aluminum washers
- Add "SS" suffix to specify stainless steel hardware
- Jumper terminals for conductors 1.00 inch diameter or larger are EHV rated
- Die Size: 10CD
- Minimum Press Tons: 60"

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	JTS10
Compression Method	Uni-Grip (single die system)
Die Size	10CD
EU RoHS Indicator	No
Material & Connection Method	Aluminum Compression
Number of Bolt Holes	0
Number of Pad Holes	2
Number of Tees	0
Press Minimum	12 to
Product Category	Compression Jumper Terminal
Tension Range	0 lb
UPC	096359495321



Dimensions

Angle - Pad	0 °
Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Outside	0 in
Diameter - Pad Bolt	0 in
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	10.4 in
Messenger Diameter Range	0 - 0
Nominal Guy Wire Size	0 in
Thickness - Pad	0 in
Weight	1.45 lb
Width - Pad	2.2 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Conductor Compatibility	ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Parakeet-556.5-24/7;ACSR-Dove-556.5-26/7;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37;AAC-Orchid-636-37
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	0 in
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-JTS10-SPEC-EN | REV 6/2024