

HUBBELL

Power Systems

Hold Down Shackle

By ANDERSON

Catalog # [HDS1024675BNK](#)

Hold down shackles are attached to suspension clamps to provide an attachment point to hook bolt or eye bolt. The HDWC type circular hold down weights can be attached in the desired increments to provide a means of controlling conductor position by preventing excessive uplift and sway. Material: body - ductile iron or forged steel, clevis pin - galvanized steel, cotter pin - stainless steel.



Features

Used with suspension clamps to provide an attachment point to hook bolt or eye bolt when hold down weights are needed. Material: Body-Galvanized Ductile Iron, Clevis Bolt and Nut-Galvanized steel, Cotter pin-Stainless Steel, Supplied with Bolt, Nut & Cotter Pin

General

EU RoHS Indicator	No
Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	HDS Series
Strength Rating - Ultimate	10000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359460220

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	7.125 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	3.1 lb

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Logistics

Pallet Quantity 640

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Literature - Ropes Course Industry Letter \(April 2021\)](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-HDS1024675BNK-SPEC-EN | REV 6/2024