

HUBBELL Power Systems

Compression Terminal Straight, Partial Tension

By ANDERSON
Catalog # JTS20

Jumper terminals are prefilled with inhibitor. Tongue holes have NEMA spacing. Standard hardware includes one aluminum 1/2 - 13 bolt, nut, and two aluminum washers per .56 diameter hole. Jumper terminals for conductors 1.00 inch diameter or larger are EHV rated.

Features

- "Jumper terminals are prefilled with inhibitor
- Standard hardware includes Aluminum 1/2-13 bolt, nut and two aluminum washers
- Add "SS" suffix to specify stainless steel hardware
- Jumper terminals for conductors 1.00 inch diameter or larger are EHV rated
- Die Size: 20CD
- Minimum Press Tons: 100"

General

Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	JTS20
Compression Method	Uni-Grip (single die system)
Die Size	20CD
EU RoHS Indicator	No
Material & Connection Method	Aluminum Compression
Number of Bolt Holes	0
Number of Pad Holes	4
Number of Tees	0
Press Minimum	100 to
Product Category	Compression Jumper Terminal
Tension Range	0 lb
UPC	096359384175



Dimensions

Angle - Pad	0 °
Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Outside	0 in
Diameter - Pad Bolt	0 in
Insulator / Conductor Hole Spacing	0 in
Length Before Compression	18.4 in
Messenger Diameter Range	0 - 0
Nominal Guy Wire Size	0 in
Thickness - Pad	0 in
Weight	8.026 lb
Width - Pad	4 in

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Conductor Compatibility	ACSR-Joree-2515-76/19; AAC-Lupine-2500-91
Conductor Diameter (Main) - Maximum	0 in
Conductor Diameter (Main) - Minimum	0 in
Conductor Diameter (Main) Range	0 - 0
Conductor Diameter - Maximum	0 in
Messenger Diameter - Maximum	0 in
Messenger Diameter - Minimum	0 in

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-JTS20-SPEC-EN | REV 6/2024