

# HUBBELL

## Power Systems

### Hot Line Link, Oval-Eye Clevis

By ANDERSON  
Catalog # [HOEC202725](#)

Hot line oval-eye ball is used to attach ball and socket insulators to other associated hardware within an insulator string. Shoulders are provided to accommodate hot line tools.



#### Features

- Hot Line Link, Oval-Eye Ball: 0.810" Thick. With 0.810" Dia. Hole
- UTS 30,000 lb
- Material: Body-Galvanized Forged steel, Clevis Pin-Galvanized steel, Cotter pin-Stainless steel
- Bolt and nut may be substituted for clevis pin by adding suffix "BNK" to catalog number
- Shield nut can be supplied by adding suffix "SN" to catalog number

#### General

Coupling Orientation	Rotated
EU RoHS Indicator	No
Extension Link Type	Oval-Eye Clevis
Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	H & F Series
Strength Rating - Ultimate	20000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359314493

#### Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	27.25 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	2.94 lb

#### Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

#### Logistics

Pallet Quantity	240
-----------------	-----

#### Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-HOEC202725-SPEC-EN | REV 6/2024