

# HUBBELL Power Systems

## Hot Line Link, Socket Y-Clevis

By ANDERSON

Catalog # [HSYC3090](#)

Hot line ball clevises are used to attach ball and socket insulators to other associated hardware within an insulator string. Shoulders are provided to accommodate hot line tools and the bent bolt in the Y-section provides an additional point of articulation within an assembly.



\*Representative Image

### Features

- "Material: Body-Galvanized ductile iron, Hardware-Galvanized steel, Cotter Pin-Stainless steel
- For use with ANSI class 52-3 & 52-5 insulators
- Shield nut can be supplied by adding suffix "SN" to catalog number"

### General

Catalog Number	HSYC3090
Coupling Orientation	Rotated
EU RoHS Indicator	No
Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	HSYC Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359316909

### Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	9.688 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	3.528 lb

### Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

### Logistics

Pallet Quantity	450
-----------------	-----

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-HSYC3090-SPEC-EN | REV 6/2024