

HUBBELL Power Systems

Suspension Clamp

By ANDERSON
Catalog # [MS104C](#)

The MS suspension clamp is a saddle type suspension clamp designed for use on overhead ground wire. They are designed for ground wire application with galvanized steel cable with or without armor rods. Type MS may also be used to suspend copper or Copperweld® cable. Magnetic induction heating will occur.

Features

- Body & Keeper are galvanized ductile iron
- Ultimate body strength 25,000 lbs
- Bolt and nut may be substituted for clevis pin by adding suffix "BNK" to catalog number.
- The clevis bolt and clevis pin are the same diameter.
- "C" suffix indicates the suspension clamp will contain the clevis eye CA06

General

Bolt Installation Torque (Recommended)	480 in-lbs
Catalog Number	MS104C
EU RoHS Indicator	No
Fitting Type	Clevis
Material - Clamp	Ductile Iron
Material - Hardware	Galvanized Steel
Material - Pin	Stainless Steel
Material - Pin (Cotter)	Stainless Steel
Material - Socket and Clevis	Galvanized Ductile Iron
Product Category	Suspension Clamp
Strength Rating - Ultimate Body	25000 lb
Type	Ground Wire Suspension Clamps
U-Bolts	1/2 in
UPC	096359357049

Dimensions

Angle - Take-Off Maximum	30 °
Clamping - Maximum	1.04 in
Clamping - Minimum	0.5 in
Clevis Opening	1.125 in
Diameter - Clevis Pin	0.625 in
Height	2.75 in
Length	8 in
Weight	7.4 lb

Electrical Ratings

Voltage Application	Ground Wire
---------------------	-------------



Conductor Related

Clamping Range	0.5- 1.04
----------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full Literature - Ropes Course Industry Letter \(April 2021\)](#)
[Sales Drawings - MS Product Family](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-MS104C-SPEC-EN | REV 6/2024