

# HUBBELL Power Systems

## Hot Line Link, Y-Clevis Clevis

By ANDERSON  
Catalog # [HYCC30](#)

Hot line ball clevises are used to attach ball and socket insulators to other associated hardware within an insulator string. Shoulders are provided to accommodate hot line tools and the bent bolt in the Y-section provides an additional point of articulation within an assembly.



\*Representative Image

### Features

- "Material: Body-Galvanized ductile iron, Hardware-Galvanized steel, Cotter Pin-stainless steel
- Bolt and nut may be substituted for clevis pin by adding suffix "BNK" to catalog number
- Shield nut can be supplied by adding suffix "SN" to catalog number"

### General

Catalog Number	HYCC30
Coupling Orientation	Straight
EU RoHS Indicator	No
Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359317616

### Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	10.38 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	4.018 lb

### Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

### Logistics

Pallet Quantity	400
-----------------	-----

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-HYCC30-SPEC-EN | REV 6/2024