

Socket Eye

By ANDERSON
Catalog # SA13

Socket Eye, Ductile Iron, Eye: 1.375" width with 0.688" Hole,
Length: 2.06", UTS 30,000 lb; For use with ANSI class 52-3 &
52-5 insulators



*Representative Image

Features

- For use with ANSI class 52-3 & 52-5 insulators

General

Material	Ductile Iron
Material - Pin (Cotter)	Stainless Steel
Series	SA Series
Strength Rating - Ultimate	30000 lb
UPC	096359324713

Dimensions

Diameter - Eye Hole	0.688 in
Dimensions	2.25 in x 3.44 in x 1.38 in
Height	1.38 in
Insulator Throat Diameter Range	0 - 0
Length	2.25 in
Length - Coupling	2.063 in
Weight	1.481 lb
Width	3.44 in
Width - Eye	1.375 in

Logistics

Pallet Quantity	1152
-----------------	------

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)
[Sales Drawings - SA13 CUTSHEET](#)