

Compression Terminal Straight, Partial Tension

By ANDERSON
Catalog # JTS08



"Bus Support, Aluminum Bolted, Slip-Fit or Rigid, 3/4" IPS/EHIPS Tube to Insulator, 3" BC, "B" Suffix replaces standard mounting hardware with Four each Galv-Steel: HH Bolts, HH Nuts, Lock-washers and Flat-washers to mount to insulator base"

*Representative Image

Features

- "Jumper terminals are prefilled with inhibitor
- Standard hardware includes Aluminum 1/2-13 bolt, nut and two aluminum washers
- Add "SS" suffix to specify stainless steel hardware
- Jumper terminals for conductors 1.00 inch diameter or larger are EHV rated
- Die Size: 08CD
- Minimum Press Tons: 12"

General

Compression Method	Uni-Grip (single die system)
Die Size	08CD
EU RoHS Indicator	No
Material & Connection Method	Aluminum Compression
Number of Pad Holes	2
Press Minimum	12 to
Product Category	Compression Jumper Terminal
UPC	096359384137

Dimensions

Length Before Compression	9.8 in
Messenger Diameter Range	0 - 0
Nominal Guy Wire Size	0 in
Weight	0.627 lb
Width - Pad	1.7 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Conductor Compatibility	ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brahma-203.2-16/19;AAC-Canna-397.5-19
Conductor Diameter (Main) Range	0 - 0

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)