

Compression Terminal Straight, Partial Tension

By ANDERSON
Catalog # JTS09



"Bus Support, Aluminum Bolted, Slip-Fit or Rigid, 1" IPS/EHIPS Tube to Insulator, 3" BC, "B" Suffix replaces standard mounting hardware with Four each Galv-Steel: HH Bolts, HH Nuts, Lock-washers and Flat-washers to mount to insulator base"

*Representative Image

Features

- "Jumper terminals are prefilled with inhibitor
- Standard hardware includes Aluminum 1/2-13 bolt, nut and two aluminum washers
- Add "SS" suffix to specify stainless steel hardware
- Jumper terminals for conductors 1.00 inch diameter or larger are EHV rated
- Die Size: 09CD
- Minimum Press Tons: 12"

General

Compression Method	Uni-Grip (single die system)
Die Size	09CD
EU RoHS Indicator	No
Material & Connection Method	Aluminum Compression
Number of Pad Holes	2
Press Minimum	12 to
Product Category	Compression Jumper Terminal
UPC	096359482888

Dimensions

Length Before Compression	10.4 in
Messenger Diameter Range	0 - 0
Nominal Guy Wire Size	0 in
Weight	0.323 lb
Width - Pad	2.2 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Conductor Compatibility	ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37
Conductor Diameter (Main) Range	0 - 0

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)