

Compression Deadend

By ANDERSON
Catalog # [SEDA3312](#)

Compression Deadend, Conventional 2-Die, Single Tongue, for ACSR 795.0 kcmil 36/1, With Terminal



*Representative Image

Features

- For use with ACSR code name Coot
- Full tension Deadend assembly
- Joint Compound purchased separately
- Jumper Terminal & Mounting Hardware included

General

Aluminum Die	30AH
Compression Method	Conventional (2 die system)
Inhibitor Loaded	No
Material	Aluminum; Steel
Material - Body	Seamless Extruded Aluminum Alloy
Material - Eye	Galvanized Forged Steel
Material - Hardware	Aluminum Alloy
Material - Terminal	Seamless Extruded Aluminum Alloy
Number of Bolt Holes	4
Press Minimum	60 to
Product Category	Assemblies
Style	Conventional 2-Die, Single Tongue
Type	Compression
UPC	096359697428

Dimensions

Diameter - Clamping Hardware	0 in
Diameter - Outside	1.04 in
Length Before Compression	19 in
Messenger Diameter Range	0 - 0
Width - Pad	3 in

Electrical Ratings

Voltage Application	EHV; Standard
---------------------	---------------

Conductor Related

Clamping Range	0- 0
Conductor Compatibility	ACSR-Coot-795-36/1
Conductor Diameter (Main) Range	0 - 0

Logistics

Pallet Quantity	60
-----------------	----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)

[Video - Installation of Hubbell's Conventional Compression Deadends for ACSR and ACSS Conductors\(VI05053E0720\)](#)