

HUBBELL Power Systems

Connector, Parallel Groove

By ANDERSON
Catalog # LCU13

Two U-Bolt Aluminum Parallel Groove Connector



*Representative Image

Features

- For aluminum to aluminum and aluminum to copper conductor splice/ tap connections
- Sealant (XB) is recommended on all connections

General

Bolt Head Type	U-Bolt
Bolt Installation Torque (Recommended)	0 ft-lbs
Catalog Number	LCU13
Cover Available	No
EU RoHS Indicator	No
Inhibitor Loaded	No
Material	Aluminum
Material - Body	Aluminum Alloy
Material - Body Halves	Aluminum Alloy
Material - Bolt	Aluminum Alloy
Material - Bottom Member	Aluminum Alloy
Material - Casting	Aluminum Alloy
Material - Hardware	Aluminum Alloy
Material - Spacer	Aluminum Alloy
Plating	No
Product Category	Mechanical Connectors
Style	Two U-Bolt
UPC	096359320166

Dimensions

Bolt Diameter	0.5
Diameter - Bolt	0.5 in
Weight	1.078 lb

Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Brahma-203.2-16/19;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Tulip-336.1-19;AAC-Daffodil-350-19;AAC-Canna-397.5-19;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18
Conductor Diameter (Tap) - Maximum	0.741 in
Conductor Diameter (Tap) - Minimum	0.325 in
Conductor Diameter - Maximum	0.741 in
Conductor Diameter - Minimum	0.325 in
Conductor Diameter Range	0.325 - 0.741

Certifications And Compliance

UL Listed

No

Product Assets

[Catalogs - Distribution Connectors](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-LCU13-SPEC-EN | REV 6/2024