

Tee, Aluminum Compression

By ANDERSON
Catalog # [ORT2119](#)

"Tee-Taps, Aluminum Compression, Open Run Cable to Cable,
For ACSR, AAC, AAAC, ACAR, 1.426" - 1.520" Main to Tap 1.331" -
1.425"



*Representative Image

Features

- "To have the pad rotated 90 degrees, add '90' to The end of the catalog ex: ORT211990
- Tees are EHV rated where conductor dia. is 1" or larger"

General

EU RoHS Indicator	No
Material	Aluminum
Number of Pad Holes	4
Type	Tee, Aluminum Compression
UPC	096359470403

Dimensions

Run Length before Compression	25.8 in
Weight	14.700 lb
Width - Flat Bar Tap	4 in

Conductor Related

Conductor Compatibility	ACSR-Bluebird-2156-84/19; ACSR-Kiwi-2167-72/7; ACSR-Thrasher-2312-76/19; AAC-Sagebrush-2250-91
Conductor Diameter (Main) - Maximum	1.805 in
Conductor Diameter (Main) - Minimum	1.711 in
Conductor Diameter (Main) Range	1.711 - 1.805
Conductor Type	<ul style="list-style-type: none">• AAC• ACSR

Logistics

Pallet Quantity	60
-----------------	----

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)
[Sales Drawings - CC-21493 \(ORT21 Product Family\)](#)