

Tee, Aluminum Compression

By ANDERSON
Catalog # [ORT221514](#)

"Weldment Tees, Connecting Tube to Tube at 15 degrees, Tubing Main-IPS/EHIPS-1-1/2", Tubing Tap-IPS/EHIPS-1", Material: Castings- Aluminum Alloy"



*Representative Image

Features

- "Tees are EHV rated where conductor dia. is 1" or larger"

General

Material	Aluminum
Type	Tee, Aluminum Compression

Dimensions

Run Length before Compression	20.1 in
Tap Length before Compression	6.7 in
Weight	4.900 lb

Conductor Related

Conductor Compatibility	ACSR-Curlew-1033.5-54/7;ACSR-Bluejay-1113-45/7;ACSR-Finch-1113-54/19;ACSR-Bunting-1192.5-45/7;ACSR-Grackle-1192.5-54/19;ACSR-Bittern-1272-45/7;ACSR-Pheasant-1272-54/19;ACSR-Dipper-1351.5-45/7;AAC-Hawthorn-1192.5-61;AAC-Narcissus-1272-61;AAC-Columbine-1351.5-61;AAC-Carnation-1431-61;AAC-Gladiolus-1510.5-61
Conductor Diameter (Main) - Maximum	1.33 in
Conductor Diameter (Main) - Minimum	1.236 in
Conductor Diameter (Main) Range	1.236 - 1.33
Conductor Diameter (Tap) - Maximum	1.235 in
Conductor Diameter (Tap) - Minimum	1.141 in
Conductor Diameter (Tap) Range	1.141 - 1.235
Conductor Type	<ul style="list-style-type: none"> • AAC • ACSR

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)