

Compression Splice Partial Tension

By ANDERSON
Catalog # PTR10

Partial Tension Aluminum splice for 1/0 (6/1 str) ACSR, 1/0 (7 str) AAC and AAAC



*Representative Image

Features

- Meets ANSI C119.4 requirements for partial tension.

General

Compression Method	VersaCrimp or Conventional Die Tooling
Die Index	C, 167, 660, 247 or 702
Die Size	<ul style="list-style-type: none">• VC6 (all)• Kearney 737 or 747• EEI 10A
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy
UPC	096359324195

Dimensions

Length Before Compression	6.25 in
Weight	0.294 lb

Conductor Related

Conductor Compatibility	ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;AAC-Poppy-1/0-7;AAAC 6201 Alloy-Azusa-123.3-6/18
Conductor Diameter - Maximum	0.398
Conductor Diameter - Minimum	0.338
Conductor Diameter Range	0.338 - 0.398

Certifications and Compliance

UL Listed	No
-----------	----

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Sales Drawings - PTR Sales Drawing](#)