

Compression Splice Partial Tension

By ANDERSON
Catalog # [PTR205](#)

Partial Tension Aluminum splice for 2/0 (6/1 str) ACSR, 2/0 (7 str) AAC and AAAC



*Representative Image

Features

- Meets ANSI C119.4 requirements for partial tension.

General

Compression Method	VersaCrimp or Conventional Die Tooling
Die Index	659
Die Size	<ul style="list-style-type: none">• VC6 (all)• Kearney 3/4
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy
UPC	096359324201

Dimensions

Length Before Compression	5.62 in
Weight	0.294 lb

Conductor Related

Conductor Compatibility	ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;AAC-Aster-2/0-7;AAAC 6201 Alloy-Azusa-123.3-6/18
Conductor Diameter - Maximum	0.447
Conductor Diameter - Minimum	0.381
Conductor Diameter Range	0.381 - 0.447

Certifications and Compliance

UL Listed	No
-----------	----

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Sales Drawings - PTR Sales Drawing](#)