

## Compression Splice Partial Tension

By ANDERSON  
Catalog # [PTR40](#)

Partial Tension Aluminum splice for 4/0 (6/1) ACSR, 4/0 (7 str) AAC and AAAC



\*Representative Image

### Features

- Meets ANSI C119.4 requirements for partial tension.

### General

Compression Method	VersaCrimp or Conventional Die Tooling
Die Index	654
Die Size	<ul style="list-style-type: none"><li>• VC6 (all)</li><li>• Kearney 1.00, 1-2</li><li>• EEI 12A</li></ul>
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy
UPC	096359324249

### Dimensions

Length Before Compression	5.25 in
Weight	0.294 lb

### Conductor Related

Conductor Compatibility	ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;AAC-Oxlip-4/0-7;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18
Conductor Diameter - Maximum	0.565
Conductor Diameter - Minimum	0.48
Conductor Diameter Range	0.48 - 0.565

### Certifications and Compliance

UL Listed	No
-----------	----

### Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)  
[Sales Drawings - PTR Sales Drawing](#)