

Coupler, Bronze Bolted

By ANDERSON
Catalog # [STTH2010](#)

"The DHCSA is a bolted aluminum suspension clamp designed to provide enhanced conductor support and protection. The DHCSA combines a cast aluminum clamp assembly with helical aluminum alloy rod sets and EPDM rubber inserts. The rubber inserts are assembled directly onto the conductor and are held in place with helical rods. The clamp assembly is then bolted around the helical wrapped rubber supporting inserts to complete the install. Material: Clamp Body & Strap- Aluminum Alloy, Rubber Insert-EPDM Rubber, Helical Rods- Aluminum Alloy, Clamping Range: 0.543"-0.555" & Helical Rod Color Code-Black, 10 Rods Per Set"



*Representative Image

Features

- "Hex Stops on the casting allows for one-wrench installation"

General

Bolt Installation Torque (Recommended)	480 in-lbs
EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless Steel
Type	Tube to Tube Couplers
UPC	096359327004

Dimensions

Diameter - Clamping Hardware	0.5 in
Weight	4.410 lb

Electrical Ratings

Maximum Current Rating Amps Continuous	See Technical Advisor
---	-----------------------

Conductor Related

Conductor Type	Copper Bus
----------------	------------

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - C-4078 \(STTH Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)