


Terminal, Bronze Bolted

By ANDERSON  
Catalog # [SWHD050D](#)

Bronze alloy terminal for connecting copper cables of equal size to a copper flat. Tongue holes have NEMA spacing. All sizes furnished with reversible cable caps.



\*Representative Image

Features

- 1/2" dia. Hex-head clamping bolts for clamping copper cable
- Side formed pads are standard for flush mounting
- Clamping bolts have hex-stops for one-wrench installation
- Tongue holes have NEMA spacing

General

Catalog Number	SWHD050D
EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Bolt Holes	4
Number of Ground Braid Lug Holes	0
Number of Pad Holes	4
Type	Bolted Lugs & Terminals
UPC	096359328049

Dimensions

Angle - Pad	180 °
Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Dimensions	7.438 in x 4 in x 3.813 in
Height	3.813 in
Length	7.438 in
Length - Coupling	0 in

Length Before Compression	0 in
Weight	5.48 lb
Width	4 in
Width - Pad	4 in

Electrical Ratings

Maximum Current Rating Amps	0
Continuous	

Conductor Related

Conductor Diameter - Maximum	0.813 in
Conductor Diameter - Minimum	0.325 in
Conductor Diameter Range	0.325 - 0.813
Conductor Type	Copper

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Product Assets

- [Catalogs - Substation Connectors \(SA\)](#)
- [Sales Drawings - C-1357](#)
- [Sales Drawings - C-1357 \(SWHD Product Family\)](#)
- [Specifications - SWHD050D](#)
- [Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products](#)
- [Video - Hubbell Power Systems Quick Ship](#)