

Socket Y-Clevis

By ANDERSON  
Catalog # [SYC30SN](#)

Socket Y-Clevis are used to connect yoke plates or associated hardware to ball and socket insulators. The bent bolt in the Y-section provides an additional point of articulation within an assembly. Type SYCS is a short coupling version of Type SYC that offers the same articulation advantages.

Features

- "Material: Body-Galvanized ductile iron, Hardware-Galvanized steel, Cotter Pin-stainless steel
- For use with ANSI class 52-3 & 52-5 insulators
- Shield nut can be supplied by adding suffix "SN" to catalog"

General

Catalog Number	SYC30SN
Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	SYC Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359328513

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Height	0.56 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in



\*Representative Image

Insulator Throat Diameter Range	0 - 0
Length - Coupling	2.75 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	3.136 lb
Width	2.75 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Certifications And Compliance

Buy America(n) Qualified	TAA Compliant (All status valid till December 2024)
--------------------------	---

Logistics

Pallet Quantity	768
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)  
[Sales Drawings - SYC30SN CUTSHEET](#)  
[Specifications - SYC30SN](#)