


Tee, Bronze Bolted

By ANDERSON
Catalog # T2HC2HC080080

"Bolted Tees, Connecting Cable Main to Cable Tap, Cable Main- 4/0 Str.- 1000 MCM, Dia.- 0.460" -1.152", Cable Tap- 1/0 Sol.-500 MCM, Dia.- 0.325"-0.813", Material: Castings- Bronze Alloy, Hardware-Silicon Bronze or Stainless Steel"



*Representative Image

Features

- "Tee for connecting two Copper Cable mains to two Copper Cable taps
- All sizes furnished with reversible caps"

General

EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless Steel
Type	Tee, Bolted
UPC	096359328858

Dimensions

Weight	11.760 lb
--------	-----------

Conductor Related

Conductor Diameter (Main) - Maximum	1.031 in
Conductor Diameter (Main) - Minimum	0.365 in
Conductor Diameter (Main) Range	0.365 - 1.031
Conductor Diameter (Tap) - Maximum	1.031 in
Conductor Diameter (Tap) - Minimum	0.365 in
Conductor Diameter - Maximum	1.031 in
Conductor Diameter - Minimum	0.365 in
Conductor Diameter Range	0.365 - 1.031
Conductor Type	Copper

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - CC-3080 \(T2HC2HC Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)