

Tee, Bronze Bolted

By ANDERSON
Catalog # [TCC8150150](#)

"Bolted Tees, Connecting Tubing Main to Tubing Tap at 15 degrees, Tubing Main-IPS/EHIPS-2", Tubing Tap-IPS/EHIPS-1-1/4", Material: Castings- Bronze Alloy, Hardware- Bronze"



*Representative Image

Features

- "Tee for Connecting Copper Cable Main to Copper Cable Tap
- All sizes furnished with reversible cable caps"

General

EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Ground Braid Lug Holes	0
Type	Tee, Bolted
UPC	096359331117

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	6.468 lb

Electrical Ratings

Maximum Current Rating Amps Continuous	0
---	---

Conductor Related

Conductor Diameter (Main) - Maximum	1.412 in
Conductor Diameter (Main) - Minimum	0.574 in
Conductor Diameter (Main) Range	0.574 - 1.412
Conductor Diameter (Tap) - Maximum	1.412 in
Conductor Diameter (Tap) - Minimum	0.574 in
Conductor Diameter - Maximum	1.412 in
Conductor Diameter - Minimum	0.574 in
Conductor Diameter Range	0.574 - 1.412
Conductor Type	Copper

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - C-4061 \(TCC8 Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)