


## Terminal, Bronze Bolted

By ANDERSON  
Catalog # TLD32

"Terminal, Bronze Bolted, Tap Lug, Cable to Flat, Single Eye Bolt, Cable Range 0.128"-0.419" Dia. to 1/4" Thick Flat, Material: Castings-Bronze alloy, Eyebolt-High strength bronze, Hardware-Stainless steel"



\*Representative Image

### Features

- "Recommended for power or grounding applications
- can be tandem mounted side by side on NEMA 1-3/4" hole centers drilled for 1/2" bolts
- Tin plating will be supplied
- For copper cable connection to aluminum bus bar, specify tin-plated terminal with Belleville spring washer by adding suffix TPBW to catalog number, Example: TLD32TPBW"

### General

Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Ground Braid Lug Holes	0
Type	Tap Lug
UPC	096359331384

### Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Thickness - Mounting Pad Maximum	0.25 in
Weight	0.882 lb

### Electrical Ratings

Maximum Current Rating Amps Continuous	0
--	---

### Conductor Related

Conductor Diameter - Maximum	0.419 in
Conductor Diameter - Minimum	0.128 in
Conductor Diameter Range	0.128 - 0.419
Conductor Type	Copper

### Logistics

Pallet Quantity	1440
-----------------	------

### Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)