


Terminal, Bronze Bolted

By ANDERSON
Catalog # [TSBA](#)

"Terminal, Bronze Bolted, One or Two Cables to Flat, Double Eyebolt Style, Cable Dia. Range 0.162"-0.575" to 1-5/8" Flat Pad with 2 Holes, Material: Castings-Bronze alloy, Eyebolt-High strength bronze, Hardware-silicon bronze or stainless steel"



*Representative Image

Features

- "Reversible cap accommodates a wide range of cable or tubing sizes"

General

EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Ground Braid Lug Holes	0
Type	Bolted Lugs & Terminals
UPC	096359332015

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Thickness	0.375 in
Weight	7.056 lb

Electrical Ratings

Maximum Current Rating Amps Continuous	0
---	---

Conductor Related

Conductor Diameter (Main) - Maximum	1.412 in
Conductor Diameter (Main) - Minimum	0.522 in
Conductor Diameter (Main) Range	0.522 - 1.412
Conductor Diameter (Tap) - Maximum	1.063 in
Conductor Diameter (Tap) - Minimum	0.162 in
Conductor Type	<ul style="list-style-type: none"> • Copper Bus • Copper

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)

[Sales Drawings - C-3021 \(TS Product Family\)](#)

[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)

[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)