

Suspension Clamp

By ANDERSON
Catalog # TSCT2150

"Tees Bolted, Connecting Cable Main to Cable Tap, Cable Main- AAC- 900-1250 MCM, ACSR- 715.5-1113 MCM, Cable Tap- AAC- 600-900 MCM, ACSR- 556.5-795 MCM, Material: Castings- Aluminum Alloy Hardware- Aluminum Alloy"



*Representative Image

Features

- "Keeper is reversible for proper fit on different size conductors
- Anti-static spring can be supplied by adding "ARIV" to catalog number. Example, TSCT2150ARIV
- Permanent marks include the IEC standard symbol for HOT surface"

General

Bolt Installation Torque (Recommended)	300 in-lbs
EU RoHS Indicator	No
Material - Clamp	Aluminum
Material - Hardware	Galvanized Steel
Product Category	Trunnion Clamp
Strength Rating - Ultimate Body	2800 lb
Type	Standard Voltage Suspension Clamps
UPC	096359332176
With Anti-Static Springs	No

Dimensions

Angle - Take-Off Maximum	15 °
Bolt Diameter	0.500 in
Clamping - Maximum	0.563 in
Clamping - Minimum	0.316 in
Diameter - Insulator Attachment Holes	0.59375 in
Length	5.25 in
Weight	1.176 lb
Width	3.875 in

Electrical Ratings

Voltage Application	Standard
---------------------	----------

Conductor Related

Clamping Range	0.316- 0.563
Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18;AAAC 6201 Alloy-Amherst-195.7-6/18

Logistics

Pallet Quantity	1080
-----------------	------

Product Assets

[Catalogs - Transmission Connectors Catalog - Full \(CA05063E\)](#)
[Literature - Ropes Course Industry Letter \(April 2021\)](#)