

# HUBBELL Power Systems

## Turnbuckle

By ANDERSON  
Catalog # [TB34EE6](#)

Turnbuckles are used as adjustable extension links to maintain proper tower clearance on assemblies at tower end. Jaw ends are supplied with bolt, nut, and humpback cotter pin. Add "LN" suffix if jam nuts are required. Remove "BNK" suffix for type EE turnbuckles.



### Features

- "Turnbuckle, 3/4", Eye-Eye, Forged Steel, Diameter = .75", Take Up = 6.00" and Ult. Strength = 26,000 LBS
- The torque required to rotate the boss of a turnbuckle under tension can be calculated by the formula:
- $T = 2 (kdW/12)$  ft-lb
- Where: k = Friction factor (0.16)
- d = Nominal thread diameter (inches)
- W = Applied tension load (lb)
- Example: 3/4" turnbuckle under 4,000 lb tension
- $T = 2(0.16 \times .75 \times 4000 / 12) = 80$  ft-lb"

### General

EU RoHS Indicator	No
Material	Steel
Number of Bolt Holes	0
Series	TYPE EE
Strength Rating - Ultimate	26000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359492085
With Jam Nuts	No

### Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Take Up	6 in
Weight	3.822 lb

### Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

### Logistics

Pallet Quantity	540
-----------------	-----

### Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-TB34EE6-SPEC-EN | REV 6/2024