

# HUBBELL Power Systems

## Terminal, Compression

By ANDERSON  
Catalog # [VACL1038](#)

VERSAtile Aluminum Compression Terminal, 1/0 str AL/CU, 1 H,  
3/8"



\*Representative Image

### Features

Rated at 34.5 KV. UL listed for aluminum or copper conductors.  
CSA certified.

### General

Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
Die Size	*See Resources / Downloads for die selection and installation instructions
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy - Tin Plated
Material - Body	Aluminum
Number of Pad Holes	1
Physical Attribute - Number of Holes	1
Style	Pressed Tubing
UPC	096359334026

### Dimensions

Diameter - Pad Bolt	0.38 in
Dimension - Bolt Hole Size inch	0.380 in
Weight	0.098 lb

### Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18
Conductor Diameter (VersaCrimp) - Maximum	0.373 in
Conductor Diameter (VersaCrimp) - Minimum	0.146 in

### Certifications And Compliance

UL Listed Yes

### Product Assets

[Catalogs - Distribution Connectors](#)  
[Installation Manuals - VACL Terminal Die Chart](#)  
[Sales Drawings - VACL Terminal Sales Drawing](#)



**A Hubbell brand**

©2024 Hubbell Incorporated. All rights reserved  
AN-VACL1038-SPEC-EN | REV 6/2024